


# Mobile Expo Analog

Qty	<u>Video Production &amp; Graphics</u>	Qty	<u>Cameras / Lenses</u>	Qty	<u>Audio Production</u>	Qty	<u>Cable Inventory &amp; MISC Gear</u>
1	Grass Valley 3000-3, 3+1 ME,8 Key Level, 56 inputs, 48 pusbuttons + shift mode 14 Aux Buses, 2 frame stores	5	Sony 370 Hard Cameras	1	Innovason SY-80, 64 mic-line input + 16 lines , 48 out W/process	6	Triax (mini) 450 ft on reels
1	DVEOUS, Dual Twin ( 4 Channel)	1	Canon 86X 9,3mm		+ 16 out. without process, 4 AES/EBU out		6 triax (mini) 4000 or 5000 ft in truck
1	Leitch still file, 1500 fields capacity	4	Fujinon 55X 9,5mm			2	5 x Triax Harness 92 ft
2	Quad Split	1	Wide angle 20X 7mm			3	Video Mult , 10 coax, 150 ft.
1	Horizon 32 x 32 routing switcher, 5 ext. Panels	2	Sony 70is Hand Held			1	Video Mult , 10 coax, 50 ft.
1	Chyron Infnit ,060,128 mb,2SCSI express 9Gb 3 Xtended buffers,Bernouilli 230, Jazz 2gb, Zip 250 Mb	2	Fujinon 18X 8.8mm	2	Yamaha multi effect SPX-1000	5	DT-12 Audio Mult, 250 ft.
		10	Wired for 10 CCUs	1	Lexicon 200	1	DT-12 AUDIO MULT 192 FT
				2	Digicart II, w Bernouilli & Zip	1	DT-12 AUDIO MULT 150 FT
					DAT TASCAM DA-60 ,CD player, MD recorder	3	DT-12 AUDIO MULT 125 FT
				2	Telos one + one ( total 4 hybrids)	1	DT-12 AUDIO MULT 47-60-69-92 FT
						7+7	DT-12 FAN OUT
Qty	<u>Production Monitor Wall</u>	Qty	<u>Outboard Monitors</u>	Qty	<u>Intercom/Communications</u>	8	50 ft Camlocks (total 100ft)
38	9" B/W monitors	4	13" TV set	1	McCurdy 9500, 50 x 60	4	47 ft Camlocks (total 47ft)
	5" B/W monitors	3	9" TV-color monitors	15	KP-96 RTS/Telex pan, (incl. 4 rem. Panels)	10	Leitch DFS-3000 frame syncs
4	4" B/W monitors	1	9" TV-Color monitor	12	RTS Interfaces ( 4w - 2w)	2	DPS 235
4	13" B/W monitors		Extras TV/ monitors on request	12	BP-325 belt packs	1	DPS 220
2	19" color monitors	1	Vga monitor (Inscriber or Chyron)	8	RTS IFB,	2	<b>DPS-290</b>
2	14" color monitors			8	IFB belt packs	1	DPS 575 multi purpose frame syncs
18	9" color monitors			6	Motorola Walkie Talkies		Various lenght of Video, RF , XLR,
1	DVD recorder			1	Motorola base station		Power bars
1	DVD Player			2	Rts Wireless Intercom 8 belt packs		AC extensions
				1	Clearcom to RTS interface		
Qty	<u>Transmission Equipment</u>	Qty	<u>EVS / VTR Complement</u>	Qty	<u>Audio Equipment &amp; Mics</u>	12	PH-88 Telex headsets
8	RF cable TV modulators	4	SONY BVW 75	5	AKG 568 eb shotgun	10	DT-109 double sided headsets
6	TV tuners, demodulators	4	Dejaview, slomo controller	6	Audio Technica AT4071 shotgun	2	DT-180 single side headsets
		1	EVS LSM XT, 2 x 2, disk recorder	5	HMD 25 Commentator Headsets		
5	ENC, D to A converters	2	VHS	5	ClearCom commentator Box		
1	DEC, A to D converter	11	9" B/W Monitors	8	EV- 635 hand mic.		
		11	9" Color monitors	5	Sony ECM-77b, Lavaliers		
		12	5 " B/W monitors	2	Fostex power speakers		
		4	4" B/W monitors				
		1	13" RF monitors				




POWER REQUIREMENTS 208/240 V 3 PHASE

WEIGHT 87,877 LBS/39,700 KG


# Mobile Expo ANALOG

Qty	<u>Video Production &amp; Graphics</u>	Qty	<u>Cameras / Lenses</u>	Qty	<u>Audio Production</u>	Qty	<u>Cable Inventory &amp; MISC Gear</u>
1	Grass Valley 3000-3, 3+1 ME,8 Key Level, 56 inputs, 48 pusbuttons + shift mode 14 Aux Buses, 2 frame stores	5	Sony 370 Hard Cameras	1	Innovason SY-80, 64 mic-line input + 16 lines , 48 out W/process	6	Triax (mini) 450 ft on reels
1	DVEOUS, Dual Twin ( 4 Channel)	1	Canon 86X 9,3mm		+ 16 out. without process, 4 AES/EBU out		Triax (mini) 4000 or 5000 ft in truck
1	Leitch still file, 1500 fields capacity	4	Fujinon 55X 9,5mm			2	5 x Triax Harness 92 ft
2	Quad Split	1	Wide angle 20X 7mm			3	Video Mult , 10 coax, 150 ft.
1	Horizon 32 x 32 routing switcher, 5 ext. Panels	2	Sony 70is Hand Held			1	Video Mult , 10 coax, 50 ft.
1	Chyron Infnit ,060,128 mb,2SCSI express 9Gb 3 Xtended buffers,Bernouilli 230, Jazz 2gb, Zip 250 Mb	2	Fujinon 18X 8.8mm	2	Yamaha multi effect SPX-1000	5	DT-12 Audio Mult, 250 ft.
		10	Wired for 10 CCUs	1	Lexicon 200	1	DT-12 AUDIO MULT 192 FT
				2	Digicart II, w Bernouilli & Zip	1	DT-12 AUDIO MULT 150 FT
					DAT TASCAM DA-60 ,CD player, MD recorder	3	DT-12 AUDIO MULT 125 FT
				2	Telos one + one ( total 4 hybrids)	1	DT-12 AUDIO MULT 47-60-69-92 FT
						7+7	DT-12 FAN OUT
Qty	<u>Production Monitor Wall</u>	Qty	<u>Outboard Monitors</u>	Qty	<u>Intercom/Communications</u>	8	50 ft Camlocks (total 100ft)
38	9" B/W monitors	4	13" TV set	1	McCurdy 9500, 50 x 60	4	47 ft Camlocks (total 47ft)
	5" B/W monitors	3	9" TV-color monitors	15	KP-96 RTS/Telex pan, (incl. 4 rem. Panels)	10	Leitch DFS-3000 frame syncs
4	4" B/W monitors	1	9" TV-Color monitor	12	RTS Interfaces ( 4w - 2w)	2	DPS 235
4	13" B/W monitors		Extras TV/ monitors on request	12	BP-325 belt packs	1	DPS 220
2	19" color monitors	1	Vga monitor (Inscriber or Chyron)	8	RTS IFB,	2	<b>DPS-290</b>
2	14" color monitors			8	IFB belt packs	1	DPS 575 multi purpose frame syncs
18	9" color monitors			6	Motorola Walkie Talkies		Various lenght of Video, RF , XLR,
1	DVD recorder			1	Motorola base station		Power bars
1	DVD Player			2	Rts Wireless Intercom 8 belt packs		AC extensions
				1	Clearcom to RTS interface		
Qty	<u>Transmission Equipment</u>	Qty	<u>EVS / VTR Complement</u>	Qty	<u>Audio Equipment &amp; Mics</u>	12	PH-88 Telex headsets
8	RF cable TV modulators	4	SONY BVW 75	5	AKG 568 eb shotgun	10	DT-109 double sided headsets
6	TV tuners, demodulators	4	Dejaview, slomo controller	6	Audio Technica AT4071 shotgun	2	DT-180 single side headsets
		1	EVS LSM XT, 2 x 2, disk recorder	5	HMD 25 Commentator Headsets		
5	ENC, D to A converters	2	VHS	5	ClearCom commentator Box		
1	DEC, A to D converter	11	9" B/W Monitors	8	EV- 635 hand mic.		
		11	9" Color monitors	5	Sony ECM-77b, Lavaliers		
		12	5 " B/W monitors	2	Fostex power speakers		
		4	4" B/W monitors				
		1	13" RF monitors				



POWER REQUIREMENTS 208/240 V 3 PHASE

WEIGHT 87,877 LBS/39,700 KG



01	11	21	31	41	51	61
02	12	22	32	42	52	62
03	13	23	33	43	53	63
04	14	24	34	44	54	64
05	15	25	35	45	55	
06	16	26	36	46	56	
07	17	27	37	47	57	
08	18	28	38	48	58	
09	19	29	39	49	59	
10	20	30	40	50	60	