

## Chapter 59

**IMPREGNATED, COATED, COVERED OR LAMINATED TEXTILE  
FABRICS; TEXTILE ARTICLES OF A KIND  
SUITABLE FOR INDUSTRIAL USE****Notes.**

1. Except where the context otherwise requires, for the purpose of this Chapter the expression "textile fabrics" applies only to the woven fabrics of Chapters 50 to 55 and headings 58.03 and 58.06, the braids and ornamental trimmings in the piece of heading 58.08 and the knitted or crocheted fabrics of headings 60.02 to 60.06.
2. Heading 59.03 applies to:
  - (a) Textile fabrics, impregnated, coated, covered or laminated with plastics, whatever the weight per square metre and whatever the nature of the plastic material (compact or cellular), other than:
    - (1) Fabrics in which the impregnation, coating or covering cannot be seen with the naked eye (usually Chapters 50 to 55, 58 or 60); for the purpose of this provision, no account should be taken of any resulting change of colour;
    - (2) Products which cannot, without fracturing, be bent manually around a cylinder of a diameter of 7 mm, at a temperature between 15°C and 30°C (usually Chapter 39);
    - (3) Products in which the textile fabric is either completely embedded in plastics or entirely coated or covered on both sides with such material, provided that such coating or covering can be seen with the naked eye with no account being taken of any resulting change of colour (Chapter 39);
    - (4) Fabrics partially coated or partially covered with plastics and bearing designs resulting from these treatments (usually Chapters 50 to 55, 58 or 60);
    - (5) Plates, sheets or strip of cellular plastics, combined with textile fabric, where the textile fabric is present merely for reinforcing purposes (Chapter 39); or
    - (6) Textile products of heading 58.11;
  - (b) Fabrics made from yarn, strip or the like, impregnated, coated, covered or sheathed with plastics, of heading 56.04.
3. For the purpose of heading 59.05, the expression "textile wall coverings" applies to products in rolls, of a width of not less than 45 cm, suitable for wall or ceiling decoration, consisting of a textile surface which has been fixed on a backing or has been treated on the back (impregnated or coated to permit pasting).

This heading does not, however, apply to wall coverings consisting of textile flock or dust fixed directly on a backing of paper (heading 48.14) or on a textile backing (generally heading 59.07).
4. For the purpose of heading 59.06, the expression "rubberised textile fabrics" means:
  - (a) Textile fabrics impregnated, coated, covered or laminated with rubber,
    - (i) Weighing not more than 1,500 g/m<sup>2</sup>; or
    - (ii) Weighing more than 1,500 g/m<sup>2</sup> and containing more than 50% by weight of textile material;
  - (b) Fabrics made from yarn, strip or the like, impregnated, coated, covered or sheathed with rubber, of heading 56.04; and
  - (c) Fabrics composed of parallel textile yarns agglomerated with rubber, irrespective of their weight per square metre.

This heading does not, however, apply to plates, sheets or strip of cellular rubber, combined with textile fabric, where the textile fabric is present merely for reinforcing purposes (Chapter 40), or textile products of heading 58.11.
5. Heading 59.07 does not apply to:
  - (a) Fabrics in which the impregnation, coating or covering cannot be seen with the naked eye (usually Chapters 50 to 55, 58 or 60); for the purpose of this provision, no account should be taken of any resulting change of colour;
  - (b) Fabrics painted with designs (other than painted canvas being theatrical scenery, studio back-cloths or the like);
  - (c) Fabrics partially covered with flock, dust, powdered cork or the like and bearing designs resulting from these treatments; however, imitation pile fabrics remain classified in this heading;

- (d) Fabrics finished with normal dressings having a basis of amylaceous or similar substances;
- (e) Wood veneered on a backing of textile fabrics (heading 44.08);
- (f) Natural or artificial abrasive powder or grain, on a backing of textile fabrics (heading 68.05);
- (g) Agglomerated or reconstituted mica, on a backing of textile fabrics (heading 68.14); or
- (h) Metal foil on a backing of textile fabrics (generally Section IV or XV).

6. Heading 59.10 does not apply to:

- (a) Transmission or conveyor belting, of textile material, of a thickness of less than 3 mm; or
- (b) Transmission or conveyor belts or belting of textile fabric impregnated, coated, covered or laminated with rubber or made from textile yarn or cord impregnated, coated, covered or sheathed with rubber (heading 40.10).

7. Heading 59.11 applies to the following goods, which do not fall in any other heading of Section XI:

- (a) Textile products in the piece, cut to length or simply cut to rectangular (including square) shape (other than those having the character of the products of headings 59.08 to 59.10), the following only:
  - (i) Textile fabrics, felt and felt-lined woven fabrics, coated, covered or laminated with rubber, leather or other material, of a kind used for card clothing, and similar fabrics of a kind used for other technical purposes, including narrow fabrics made of velvet impregnated with rubber, for covering weaving spindles (weaving beams);
  - (ii) Bolting cloth;
  - (iii) Straining cloth of a kind used in oil presses or the like, of textile material or of human hair;
  - (iv) Flat woven textile fabrics with multiple warp or weft, whether or not felted, impregnated or coated, of a kind used in machinery or for other technical purposes;
  - (v) Textile fabrics reinforced with metal, of a kind used for technical purposes;
  - (vi) Cords, braids and the like, whether or not coated, impregnated or reinforced with metal, of a kind used in industry as packing or lubricating materials;
- (b) Textile articles (other than those of headings 59.08 to 59.10) of a kind used for technical purposes (for example, textile fabrics and felts, endless or fitted with linking devices, of a kind used in paper-making or similar machines (for example, for pulp or asbestos-cement), gaskets, washers, polishing discs and other machinery parts).

## CUSTOMS TARIFF - SCHEDULE

Tariff Item	SS	Description of Goods	Unit of Meas.	MFN Tariff	Applicable Preferential Tariffs
<b>59.01</b>		<b>Textile fabrics coated with gum or amylaceous substances, of a kind used for the outer covers of books or the like; tracing cloth; prepared painting canvas; buckram and similar stiffened textile fabrics of a kind used for hat foundations.</b>			
<b>5901.10</b>		<b>-Textile fabrics coated with gum or amylaceous substances, of a kind used for the outer covers of books or the like</b>			
5901.10.10 00	--	-Holland cloth, solely of cotton fibres	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5901.10.90 00	--	-Other	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>5901.90</b>		<b>-Other</b>			
5901.90.10 00	--	-Prepared painting canvas	KGM	7%	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5901.90.90 00	--	-Other	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>59.02</b>		<b>Tire cord fabric of high tenacity yarn of nylon or other polyamides, polyesters or viscose rayon.</b>			
<b>5902.10.00 00</b>		<b>-Of nylon or other polyamides</b>			
5902.10.00 00		-Of nylon or other polyamides	KGM	Free	LDCT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>5902.20.00 00</b>		<b>-Of polyesters</b>			
5902.20.00 00		-Of polyesters	KGM	Free	LDCT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>5902.90.00 00</b>		<b>-Other</b>			
5902.90.00 00		-Other	KGM	Free	LDCT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>59.03</b>		<b>Textile fabrics impregnated, coated, covered or laminated with plastics, other than those of heading 59.02.</b>			

## CUSTOMS TARIFF - SCHEDULE

Tariff Item	SS	Description of Goods	Unit of Meas.	MFN Tariff	Applicable Preferential Tariffs
<b>5903.10</b>		<b>-With poly(vinyl chloride)</b>			
		- - -Textile fabrics not containing man-made fibres:			
5903.10.11 00	- - -	-Of a length of 9 m or more, for use in the manufacture of umbrellas having a rib length not exceeding 69 cm; Woven fabrics of cotton, impregnated and coated, with the weight of the unimpregnated/uncoated fabrics not exceeding 120 g/m <sup>2</sup> and the total weight of the impregnated/coated fabrics exceeding 430 g/m <sup>2</sup> but not exceeding 470 g/m <sup>2</sup> , for use in the manufacture of apparel	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5903.10.19 00	- - -	-Other	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
		- - -Textile fabrics containing man-made fibres:			
5903.10.21 00	- - -	-For use in the manufacture of headbands (hat sweats), linings (including tips and sides), peaks and stiffening bands for hats or caps; Of a length of 9 m or more, for use in the manufacture of umbrellas having a rib length not exceeding 69 cm; Coated open weave fabrics, solely of yarns of polyesters, or open weave fabrics, solely of yarns of polyesters which have been extrusion or dip coated, for use in the manufacture of garden furniture, umbrellas for garden furniture or cushions for garden furniture; Woven fabrics of cotton mixed solely with polyesters, or solely of polyester staple fibres or of polyester staple fibres mixed solely with cotton, for use in the manufacture of family or recreational tents of a floor area of 3 m <sup>2</sup> or more but not exceeding 21 m <sup>2</sup>	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5903.10.29 00	- - -	-Other	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>5903.20</b>		<b>-With polyurethane</b>			
		- - -Textile fabrics not containing man-made fibres:			
5903.20.11 00	- - -	-With a leather-like coating solely of polyurethane on one side, the weight of the coating being 20% or more of the total weight of the coated fabric, for use in the manufacture of footwear or handbags; Woven fabrics, certified by the exporter to be products that have been impregnated with polyurethane which has been coagulated, of a total weight, including the impregnation, exceeding 240 g/m <sup>2</sup> , for use in the manufacture of clothing accessories, parts of garments or trimmings for garments, including labels, badges and similar articles of a kind normally sewn to the outer part of wearing apparel	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free

## CUSTOMS TARIFF - SCHEDULE

Tariff Item	SS	Description of Goods	Unit of Meas.	MFN Tariff	Applicable Preferential Tariffs
5903.20.19	00	---Other	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
		---Textile fabrics containing man-made fibres:			
5903.20.21	00	---Heat seal tape; With a leather-like coating solely of polyurethane on one side, the weight of the coating being 20% or more of the total weight of the coated fabric, for use in the manufacture of footwear or handbags; Woven fabrics, certified by the exporter to be products that have been impregnated with polyurethane which has been coagulated, of a total weight, including the impregnation, exceeding 240 g/m <sup>2</sup> , for use in the manufacture of clothing accessories, parts of garments or trimmings for garments, including labels, badges and similar articles of a kind normally sewn to the outer part of wearing apparel; Woven fabrics of cotton mixed solely with polyesters, or solely of polyester staple fibres or of polyester staple fibres mixed solely with cotton, for use in the manufacture of family or recreational tents of a floor area of 3 m <sup>2</sup> or more but not exceeding 21 m <sup>2</sup> ; Woven tape, containing 50% by weight of cotton and 50% by weight of rayon fibres, coated with an adhesive, for use in the manufacture of footwear; Woven fabrics, solely of polyester filament yarns, the weight of the coated or covered fabric not exceeding 150 g/m <sup>2</sup> , for use in the manufacture of aircraft	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5903.20.22	00	---Woven fabrics, solely of single, non-textured nylon filament yarns, coated on one side with non-cellular polyurethane, with the total weight of the coated fabric not exceeding 72 g/m <sup>2</sup> , for use in the manufacture of family or recreational tents of a floor area of 3 m <sup>2</sup> or more but not exceeding 21 m <sup>2</sup> , or tent flies	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5903.20.23	00	---Imitation leather, containing 60% or more by weight of man-made fibres, valued at \$13/m <sup>2</sup> or more; Poromeric materials, with a water vapour permeability of 0.5 mg/cm <sup>2</sup> /hr or more but not exceeding 11 mg/cm <sup>2</sup> /hr, excluding materials with a backing composed solely of woven or knitted fabrics, for use in the manufacture of footwear	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5903.20.24	00	---Weft-knit fabric of polyester, nylon or poly(m-phenylene isophthalamide), coated on one side with a non-cellular polyurethane, certified by the exporter to have been transfer-coated, for use in the manufacture of apparel	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5903.20.25	00	---Four-layer fabric consisting of a first layer of woven polyester or nylon fabric with or without elastomeric yarns, a second layer of cellular polytetrafluoroethylene, a third layer of non-cellular polyurethane and a fourth layer of woven or knit fabric of polyester or nylon, for use in the manufacture of water-resistant or waterproof, breathable recreational outerwear, including alpine hiking and climbing, skiing or mountaineering apparel	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free

## CUSTOMS TARIFF - SCHEDULE

Tariff Item	SS	Description of Goods	Unit of Meas.	MFN Tariff	Applicable Preferential Tariffs
5903.20.29 00	- - - -	-Other	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>5903.90</b>	<b>-Other</b>				
5903.90.10 00	- - -	-Textile fabrics not containing man-made fibres	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
	- - -	-Textile fabrics containing man-made fibres:			
5903.90.21 00	- - - -	-Heat seal tape;Woven fabrics of cotton mixed solely with polyesters, or solely of polyester staple fibres, or of polyester staple fibres mixed solely with cotton, for use in the manufacture of family or recreational tents of a floor area of 3 m <sup>2</sup> or more but not exceeding 21 m <sup>2</sup>	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5903.90.22 00	- - - -	-Warp knit fabrics, of polyester filaments and polyester staple fibres, partially coated with hot-melt adhesive, of a weight not exceeding 55 g/m <sup>2</sup> , for use in the manufacture of apparel	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5903.90.23 00	- - - -	-Other, of textured polyester filament yarns, partially coated with hot-melt adhesive, with a 4% minimum stretch in the warp and a 12% minimum stretch in the weft as measured by specification ASTM D3107-75, of a weight not exceeding 95 g/m <sup>2</sup> , for use in the manufacture of apparel	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5903.90.24 00	- - - -	-Other, of textured and non-textured polyester filament yarns, partially coated with hot-melt adhesive, with a 4% minimum stretch in the warp and a 12% minimum stretch in the weft as measured by specification ASTM D3107-75, of a weight exceeding 70 g/m <sup>2</sup> but not exceeding 95 g/m <sup>2</sup> , for use in the manufacture of apparel	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5903.90.25 00	- - - -	-Stitch-bonded, warp knit fabrics, solely of polyesters, coated on one side with cellular acrylic polymer, for use as ticking in the manufacture of mattresses or mattress supports	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5903.90.26 00	- - - -	-Woven fabric of polyester filaments coated on one side with two layers of acrylic polymers and on the other side with a layer of polyvinyl acetate polymer, for use in the manufacture of internal roller shade systems	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5903.90.27 00	- - - -	-The following for use in the manufacture of water-resistant or waterproof, breathable recreational outerwear, including alpine hiking and climbing, skiing or mountaineering apparel: Three-layer fabric consisting of a middle layer of cellular polytetrafluoroethylene, having a woven polyester or nylon fabric with or	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free

## CUSTOMS TARIFF - SCHEDULE

Tariff Item	SS	Description of Goods	Unit of Meas.	MFN Tariff	Applicable Preferential Tariffs
		without elastomeric yarns on one side and a woven or knit fabric of polyester or nylon on the other side; Four-layer fabric consisting of a first layer of woven polyester or nylon fabric with or without elastomeric yarns, a second layer of cellular polytetrafluoroethylene, a third layer of non-cellular polyurethane and a fourth layer of woven or knit fabric of polyester or nylon			
5903.90.29 00	- - -	-Other	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>59.04</b>		<b>Linoleum, whether or not cut to shape; floor coverings consisting of a coating or covering applied on a textile backing, whether or not cut to shape.</b>			
<b>5904.10.00 00</b>		<b>-Linoleum</b>	MTK	7%	LDCT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free GPT: 5%
<b>5904.90</b>		<b>-Other</b>			
5904.90.10 00	- -	-Floor coverings, with a base consisting of needleloom felt or nonwovens	MTK	13.5%	LDCT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free GPT: 5%
5904.90.90 00	- -	-Other	MTK	18%	LDCT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free GPT: 12%
<b>5905.00</b>		<b>Textile wall coverings.</b>			
5905.00.10 00	- -	-Backed with wallpaper base (hanging stock), whether or not coated or pre-pasted; Of jute backed with paper	MTK	5%	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5905.00.90 00	- -	-Other	MTK	14%	LDCT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free GPT: 10%
<b>59.06</b>		<b>Rubberized textile fabrics, other than those of heading 59.02.</b>			
<b>5906.10</b>		<b>-Adhesive tape of a width not exceeding 20 cm</b>			

## CUSTOMS TARIFF - SCHEDULE

Tariff Item	SS	Description of Goods	Unit of Meas.	MFN Tariff	Applicable Preferential Tariffs
5906.10.10 00	--	For use in the manufacture of thermionic, cold cathode or photo-cathode valves and tubes	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5906.10.90 00	--	-Other	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>-Other:</b>					
<b>5906.91 --Knitted or crocheted</b>					
5906.91.10 00	--	Cellular chloroprene rubber sheets with a knitted nylon fabric laminated to one or both sides	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>--Other:</b>					
5906.91.91 00	---	For use in the manufacture of apparel	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5906.91.99 00	---	-Other	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>5906.99 --Other</b>					
<b>--Textile fabrics not containing man-made fibres:</b>					
5906.99.11 00	---	For use in the manufacture of apparel	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5906.99.19 00	---	-Other	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>--Textile fabrics containing man-made fibres:</b>					



## CUSTOMS TARIFF - SCHEDULE

Tariff Item	SS	Description of Goods	Unit of Meas.	MFN Tariff	Applicable Preferential Tariffs
5906.99.21	00	---Woven fabrics of yarns of synthetic filaments coated with a mixture of styrene-butadiene rubber and resorcinol-formaldehyde resin for use in the manufacture of conveyor belts or conveyor belting; Woven fabrics, solely of nylon or solely of polyester, coated or covered with rubber, for use in the manufacture of inflatable boats or inflatable life preservers	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5906.99.22	00	---Other, for use in the manufacture of conveyor or transmission belts or belting; Tire cord fabric for use in the manufacture of pneumatic tires	KGM	Free	LDCT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5906.99.23	00	---Woven fabrics, coated or impregnated with styrene-butadiene rubber or butadiene rubber, of high tenacity yarns solely of nylon filaments or of high tenacity yarns of polyester filaments and nylon filaments, of a weight not exceeding 1,000 g/m <sup>2</sup> , for use as a stabilizing/reinforcing fabric in the manufacture of unvulcanized, calendered rubber of a kind used in the manufacture of snowmobile track and industrial track	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5906.99.24	00	---Impregnated, coated, covered or laminated with rubber, other than neoprene rubber, for use in the manufacture of apparel	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5906.99.29	00	---Other	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>5907.00</b>		<b>Textile fabrics otherwise impregnated, coated or covered; painted canvas being theatrical scenery, studio back-cloths or the like.</b>  ---Textile fabrics otherwise impregnated, coated or covered:			
5907.00.11	00	---Holland cloth, solely of cotton fibres	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5907.00.12	00	---Woven fabrics, solely of non-melting, heat stabilized polyacrylonitrile fibres produced by the oxidization of polyacrylonitrile	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5907.00.13	00	---Oilcloth	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free

## CUSTOMS TARIFF - SCHEDULE

Tariff Item	SS	Description of Goods	Unit of Meas.	MFN Tariff	Applicable Preferential Tariffs
5907.00.16	00	---Other, solely of cotton, containing 2 ply yarns, impregnated with materials that are predominantly not of plastic or rubber to achieve a hydrostatic pressure of more than 36 cm of water, based on ISO 811-1981 using a rate of increase of water pressure of 60 cm of water/min, and a spray rating of ISO 4 or higher, based on ISO 4920-1981, all values taken in a standard temperate atmosphere based on ISO 139-1973 using distilled or fully deionized water at 20 ± 2 °C, the impregnated fabric weighing 250 g/m <sup>2</sup> or more but not exceeding 400 g/m <sup>2</sup> and valued at \$4.50/m <sup>2</sup> or more, for use in the manufacture of jackets, coats or hats	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5907.00.17	00	---Other, for use in the manufacture of apparel	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5907.00.18	00	---Other, not containing man-made fibres	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5907.00.19	00	---Other, containing man-made fibres	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
		---Painted canvas being theatrical scenery, studio back-cloths or the like:			
5907.00.21	00	---Of a kind used as photographic, cinematographic or television studio equipment	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5907.00.29	00	---Other	KGM	14%	LDCT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>5908.00</b>		<b>Textile wicks, woven, plaited or knitted, for lamps, stoves, lighters, candles or the like; incandescent gas mantles and tubular knitted gas mantle fabric therefor, whether or not impregnated.</b>			
5908.00.10	00	---Textile wicks, whether or not plaited, processed or with core, for use in the manufacture of wax candles or tapers or to be employed in oil-burning sanctuary lamps	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5908.00.90	00	---Other	KGM	14%	LDCT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free GPT: 10%

## CUSTOMS TARIFF - SCHEDULE

Tariff Item	SS	Description of Goods	Unit of Meas.	MFN Tariff	Applicable Preferential Tariffs
<b>5909.00</b>		<b>Textile hosepiping and similar textile tubing, with or without lining, armour or accessories of other materials.</b>			
5909.00.10 00	--	Fire hose	MTR	12%	LDCT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free GPT: 10%
5909.00.90 00	--	Other	MTR	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>5910.00.00 00</b>		<b>Transmission or conveyor belts or belting, of textile material, whether or not impregnated, coated, covered or laminated with plastics, or reinforced with metal or other material.</b>	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>5911</b>		<b>Textile products and articles, for technical uses, specified in Note 7 to this Chapter.</b>			
<b>5911.10</b>		<b>-Textile fabrics, felt and felt-lined woven fabrics, coated, covered or laminated with rubber, leather or other material, of a kind used for card clothing, and similar fabrics of a kind used for other technical purposes, including narrow fabrics made of velvet impregnated with rubber, for covering weaving spindles (weaving beams)</b>			
5911.10.10 00	--	Blankets, lapping or blanketing to be employed in offset printing machinery	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5911.10.20 00	--	Belting, of a thickness not exceeding 2.8 mm and a width exceeding 350 mm, of nylon, polyester or aramid, for use in the manufacture of conveyor belts; Belts and developer sleeves for use in the manufacture of contact printers; Other blankets, lapping or blanketing; Transmission belting, excluding belting of trapezoidal cross-section (V or multi V), whether or not embossed, for use in the manufacture of transmission belts	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5911.10.90 00	--	Other	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>5911.20</b>		<b>-Bolting cloth, whether or not made up</b>			

## CUSTOMS TARIFF - SCHEDULE

Tariff Item	SS	Description of Goods	Unit of Meas.	MFN Tariff	Applicable Preferential Tariffs
5911.20.10	00	-- For sifting flour in flour mills; For use in the manufacture of screens for printing	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5911.20.90	00	-- Other	KGM	Free	LDCT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
<b>-Textile fabrics and felts, endless or fitted with linking devices, of a kind used in paper-making or similar machines (for example, for pulp or asbestos-cement):</b>					
5911.31.00	00	-- Weighing less than 650 g/m <sup>2</sup>	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5911.32.00	00	-- Weighing 650 g/m <sup>2</sup> or more	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5911.40		<b>-Straining cloth of a kind used in oil presses or the like, including that of human hair</b>			
5911.40.10	00	-- Filtering fabric, solely of non-textured polyester filaments, with a loom width exceeding 3 metres, for use in the manufacture of cesium formate	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5911.40.90	00	-- Other	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free
5911.90.00	00	-Other	KGM	Free	LDCT, GPT, UST, MT, CIAT, CT, CRT, IT, NT, SLT, PT, COLT, JT, PAT, HNT, KRT, CEUT, UAT: Free